

DX1001-W

The DX modular housing arrangement offers a flexible and space conscious solution to integrate our innovative DXO Cartridge in to both new and existing systems. The Delta-Xero system can be configured up to 3 cartridges in parallel as a single unit in a compact and easily maintainable layout.

The unit can be supplied with a number of standard options to provide an effective fluid conditioning and monitoring package to suit the majority of systems. The flexibility of the unit allows tailoring to customer's specific requirements.






DX1001-W


Drive Input	Electric or Pneumatic							
Connection Ports	3/8"BSP In & Out							
Flow Indicator	Visual							
Suggested System Volume	Up to 4500ltrs @ 32cSt							
Particulate Removal	From 0,1 µ							
Weight	15 kg							
Measure	H 524 mm x D 261 mm x L 442 mm							
Material	SS316							
DXO Cartridge QTY	1							
Flow Rate varies depending on viscosity, pressure and temperature	Approx flow at 2.7	32 cSt 1.25 l/min	46 cSt 1.0 l/min	68 cSt 0.8 l/min	100 cSt 0.6 l/min	220 cSt 0.4 l/min	320 cSt 0.2 l/min	460 cSt 0.1 l/min
	bar: Oil Volume	4500ltrs	3500ltrs	3000ltrs	2400ltrs	1800ltrs	800ltrs	400ltrs


© 20 2 Delta-Xero All Rights Reserved. All information contained in this publication is indicative only and may be subject to change without prior notice




General Arrangement + Schematic









Cartridge Data: DXO

Contaminated weight:	Up to 4.5kg per DXO			
Water holding capacity, free and bound:	Approx. 2600ml			
Material insert:	PP Cellulose mix			





